

CGA Compressed Gas Cylinder Valve Outlets & Connections

No	Dimensions
001	Φ 21.7-14NGO-RH
002	M22-2.0PGO-RH
003	Φ 20-14NGO-LH
004	Φ 24.4-14NGO-RH
005	Φ 26.3-14NGO-RH
006	Φ 7/8"-14NGO-RH
007	Φ 0.88"-14NGO-LH

No	Dimensions
008	Φ 26.3-14NGO-RH
009	Φ 0.86"-14NGO-RH
010	Φ 21.7-14NGO-RH
011	Φ 24.4-14NGO-RH
012	Φ 21.7-14NGO-RH
013	PF5/8"-14NGO-LH
014	PF5/8"-14NGO-RH

No	Dimensions
300	.825"-14NGO-RH(M) .825"-14(F)
320	.825"-14NGO-RH(M) .830"-14(F)
510	.885"-14NGO-LH(F) .880"-14(F)
540	.930"-14NGO-RH(M) .908"-14(F)
580	.965"-14NGO-RH(F) .960"-14(M)
992 (British Oxygen)	.910"-14NGO-RH(F) .898"-14(M)
993 (British Acetylene)	.910"-14NGO-LH(F) .898"-14(M)

These dimensional drawings illustrate cylinder valve outlets and connections:
 The drawing at the left illustrates the cylinder valve outlet.
 The one of right illustrates it's mating regulator or valve connection.